

To Order Optional Lenses, Substitute Lens Ordering Code Shown Below

SAMPLE CATALOG NUMBER: 2SPG332-FS01

FS – Flat Steel
FA – Flat Aluminum
RA – Regressed Aluminum

2 SP G 3 32 – FS 01

Lens Identification	Material*	Lens Code	Door Frames	
			FS/FA	RA
Pattern 12 Acrylic**	A	01	X	X
MA-6**	A	06	X	–
Frost Glaze (opal) .187" thick	A	08	X	–
DB-12 .125" thick**	A	12	X	X
Pattern 12 R.F.I. .125" thick	A	12RF	X	X
Pattern 12 silver tint .125" thick	A	12ST	X	X
DB-12 .156" thick	A	14	X	X
Pattern 15 .200" thick	A	15	X	–
DB-12 .170" thick	A	16	X	–
DB-19 .156" thick**	A	19	X	X
Pattern 19 R.F.I. .156" thick	A	19RF	X	X
Pattern 19 silver tint .156" thick	A	19ST	X	X
Pattern 12 .125" thick**	A	21	X	X
DB-12 white .125" thick	A	22	X	X
KSH Uvalite .125" thick	A	23	X	X
Holophane 8224	A	24	X	–
Holophane 8224+8243 overlay	A	24Y	X	–
KSH Acri-Tuff .140" thick	DR	26	X	X
1/2"x1/2"x1/2" Silver Paracube I	P	30	X	X
1/2"x1/2"x1/2" Gold Paracube I	P	31	X	X
1/2"x1/2"x1/2" Silver Paracube I	A	32	X	X
1/2"x1/2"x1/2" Gold Paracube I	A	33	X	X
1-1/2"x1-1/2"x1" Silver Paracube II	P	34	X	X
1-1/2"x1-1/2"x1" Gold Paracube II	P	35	X	X
1-1/2"x1-1/2"x1" Silver Paracube II	A	36	X	X
1-1/2"x1-1/2"x1" Gold Paracube II	A	37	X	X
1/2"x1/2"x1/2" white eggcrate	P	42	X	X
1/2"x1/2"x1/2" white eggcrate	A	43	X	X
Holophane 6244 replaced by 6255 (see lens code 88)				
Holophane 6250	A	50	X	–
Holophane 6251 R.F.I.	A	51RF	X	–
3/4"x3/4"x1/2" Silver Paracube IV	P	52	X	X
3/4"x3/4"x1/2" Gold Paracube IV	P	53	X	X
3/4"x3/4"x1/2" Silver Paracube IV	A	54	X	X
3/4"x3/4"x1/2" Gold Paracube IV	A	55	X	X
Vanguard Gridless Octex .187" thick**	DR	56	X	–
KSH 90 matte white	A	65	X	X
PSI Asymmetric IV .125" thick	A	72	X	X
Pattern 12 Lexan .125" thick	L	79	X	X
Holophane 6245 .187" thick	A	81	X	–
DB-12 .187" thick	A	83	X	–
Holophane 6255	A	88	X	–
KSH 20 silver tint .140" thick	A	92	X	X
KSH K-Pan drop dish	A	93	X	–
KSH 20 .140" thick	A	95	X	X
KSH 23 .100" thick	A	96	X	X
KSH 23 .125" thick	A	97	X	X
Frost Glaze (opal) .125" thick	A	101	X	X
DB-19 smoke tone .156" thick	A	104	X	X
PSI 21 High impact (21DR) .125" thick	DR	110	X	X
PSI 2182 Lensgard .250" thick	A+L	114	X	–
DB-19 .187" thick	A	125	X	–
DB-12 .125" minimum	A	126	X	X
Pattern 12 .187" thick	A	131	X	–
PSI 21 High impact (21DR) .187" thick	DR	145	X	–
ALP PL3	P	PL3	X	X
ALP PL3	A	PA3	X	X

*Material: A = Acrylic, DR = DR (impact resistant) acrylic, G = Glass, L = Lexan (polycarbonate), P = Polystyrene

**See spec. sheet 803-CL for more information on the 01, 06, 12, 19, 21 and 56 lenses.

For lenses not shown on matrix, contact factory representative.

